



Country Fact Sheet Motors

Mexico



Regional Characteristics

Voltage 3 ~ 480V ± 10%



Frequency 60 Hz

Approval Mark **UL recognized or UL listed**

Standard UL 1004

Scope Not mandatory but strict market requirement due to insurance and employer safety reasons. Proofs the accordance with UL standards and verifies product testing regarding safety aspects like flammability.

Marking

 (for components) or  (for devices)

Energy Efficiency **Norma Oficial Mexicana**

Regulation NOM 016 ENER 2016

Mandatory Efficiency Class Premium (equates to IE3)

Scope

- Rated output power from 0.746 kW up to 373 kW
- Rated voltage up to 600 V
- Rated frequency 50 and 60 Hz
- 2-, 4-, 6- and 8-pole
- For continuous duty operation

Exemptions

- Motors other than S1, S3 (duty factor ≥ 80%), S6 (cont. duty with intermittent loads), S9 (cont. duty with non-periodic load and speed variations)
- Motors for heavy environmental conditions like ambient temperature above +60°C or below -30°C, installation altitude above 4000m
- Pole-changeable motors

Marking

- Norma Oficial Mexicana Prüfzeichen (NOM)