

Country Fact Sheet Motors



European Union



Regional Characteristics

Voltage 3 ~ 400V ± 10%
1 ~ 230V ± 10%

Frequency 50 Hz

Approval Mark CE Conformity

Standard EN IEC 60034

Regulation Low Voltage Directive 2014/35/EU
ErP Directive 2009/125/EG
RoHS Directive 2011/65/EU

Scope All machines and electronic devices which are affected by any EU Directive.

Marking 

Energy Efficiency Ecodesign Directive

Regional Standard Directive 2009/125/EC

Regulation Commission Regulation (EC) No. 640/2009 and (EU) No. 4/2014 (2017)

Mandatory Efficiency Class IE3 (or IE2 – motors for use with VSD)

Scope

- Rated output power from 0.75 up to 375 kW
- Rated voltage from 50 up to 1000 V
- Rated frequency 50 and 60 Hz
- 2-, 4- and 6-pole
- For continuous duty operation

Exemptions

- Motors other than S1, S3 (duty factor > 80%) or S6 (duty factor > 80%)
- Exclusively suitable for inverter operation
- Ex-motors
- Brake Motors (The brake is inside the motor housing)
- Motors for heavy environmental conditions like ambient temperature above +60°C or below -30°C, installation altitude above 4000m
- Pole-changeable motors
- With Integral fans and blower motors
- Motors that share common components with the driven unit and cannot operate as a motor if separated from it
- Motors specifically designed and specified to operate wholly immersed in a liquid

Marking

- IE-Class
- Nominal efficiency (η) at 50%, 75% and 100 % load
- If applicable "Use with VSD only" (->IE2)

From 1st July 2021, new requirements for small powers <0.75 kW will enter into force. In addition several exemptions will decline. The next page provides an overview on the upcoming requirements. For more information and changeover support, take a look at our [ecodesign-page](#).

Country Fact Sheet Motors – Update from 1st July 2021



European Union



Regional Characteristics

Voltage
3 ~ 400V ± 10%
1 ~ 230V ± 10%

Frequency 50 Hz

Approval Mark CE Conformity

Standard EN IEC 60034

Regulation Low Voltage Directive 2014/35/EU
ErP Directive 2009/125/EG
RoHS Directive 2011/65/EU

Scope All machines and electronic devices which are affected by any EU Directive.

Marking



Energy Efficiency Ecodesign Directive

Regional Standard Directive 2009/125/EC

Regulation Commission Regulation (EU) No. 2019/1781

Mandatory Efficiency Class IE2 from 0.12 kW
IE3 from 0.75 kW

Scope

- Directive 2009/125/EC
- Commission Regulation (EU) No. 2019/1781
- IE2 from 0.12 kW, IE3 from 0.75 kW
- Rated output power from 0.12 up to 1000 kW
- Rated voltage from 50 up to 1000 V
- Rated frequency 50 and 60 Hz
- 2-, 4-, 6- and 8-pole
- For continuous duty operation

Exemptions

- Motors other than S1, S3 (duty factor ≥ 80%) or S6 (duty factor ≥ 80%)
- Exclusively suitable for inverter operation
- Ex-motors
- Motors with integrated variable speed drive as integral part of the motor
- Motors for heavy environmental conditions like ambient temperature above +60°C or below -30°C, installation altitude above 4000m
- Pole-changeable motors
- Motors placed on the market before 1st July 2029 as substitutes for identical motors integrated in products placed on the market before 1st July 2022, and specifically marketed as such
- Motors that share common components with the driven unit and cannot operate as a motor if separated from it
- Motors specifically designed and specified to operate wholly immersed in a liquid

Marking

- IE-Class
- Nominal efficiency (η) at 50%, 75% and 100 % load

For more information and changeover support, take a look at our [ecodesign page](#).

Current status March 2020