


Automation solutions for warehouse logistics.



As easy as that.



70 years
experience
in the area of
warehouse
logistics.

As one of the leading specialists in drive and automation technology, with extensive know-how and a worldwide network of experts in intralogistics, we always work with you closely to find the very best solution. We set your ideas in motion with great enthusiasm and an eye for what works, regardless of whether you want to improve existing equipment or develop a completely new machine.

In line with your individual requirements and ideas, we provide you with comprehensive support – from the planning of individual assemblies or complete materials handling systems, to commissioning of the final equipment you need.

We develop innovations for warehouse logistics with ease:

- Experienced industry experts understand your requirements and the tasks you are faced with
- Innovative hardware and software for the implementation of energy-efficient solutions
- Reliable drive systems for typical warehouse applications
- Use of open standards
- Global production with uniform Lenze quality standards
- Worldwide efficient logistics concept
- Global service network and range of training courses offered



Adjusting to reality.

Shorter innovation cycles, aggressive competitors, and competitive pricing pressure, are challenges that mechanical engineering companies are increasingly having to deal with. Good reasons for us to make your everyday work easy.

With our Engineering Toolchain, we offer tools for consistent engineering in the different phases of your equipment's lifecycle. They have been specially designed for mechatronic engineering tasks and are precisely tailored to both the user and the work involved.

In order to enable the performance of very different automation tasks, we offer intelligent solutions for controller-based automation or drive-based automation. Profit from our modular, scalable and coherent mechatronics kits. With reliable technologies, long-lasting quality, and easy handling of all products.

This not only reduces the variety of drives you use, but also your entire engineering process. In the end, this works to everyone's advantage.

Efficient software solutions


- Consistent engineering tool chain over the entire lifecycle
- Intelligent motion control with standardized technology functions

Reduced amount of engineering work

Appropriate automation solutions

The right system and the right products for every machine



Reduced investment in drives and automation



Exactly what you need for your warehouse logistics application.

We work with you to develop intelligent automation solutions for your systems for the reliable flow of material – from small materials handling applications to complete logistics systems.


You can rely on our easy software engineering tools, the use of open standards, the right drive design, and energy-efficient solutions. Create your successful system at greater speed, with less need for space and for maximum availability.



Software engineering made easy

With Lenze FAST, our application software toolbox, you can combine intelligent standardized software modules for very different technology modules in a single template and thus create your machine software


the easy way. This reduces your motion software engineering work by up to 80%, which in turn leads to a considerable reduction of time needed to develop basic functions of your machine.



Open standards

Lenze automation systems are open! Due to the use of market standards, we can network with the manufacturers of other control and drive systems at any time. This enables easy integration into higher-level line topologies. In addition,

this openness makes everything and everybody ready for the future, including the mechanical engineering company and the end user of the product. Keep your core competence in your company and secure your advantage over competitors.




Industry 4.0 – Cooperation skills as a new core competence.

Mechanical engineering has always been characterized by a high degree of orientation to the customer, converting their needs into real technical solutions. With Industry 4.0, possibilities and new facets offer fresh opportunities from outside the industry of mechanical engineering. Anyone who cooperates with partners faster and more effectively, and who integrates their on-going processes, will always win in competition with others.

Collaborative skills generate a high level of expertise to manage trends and end user requirements for the next generation of machines, allowing technical solutions and innovations that bring competitive advantages to be created:

- What benefits are most important to you?
- What technical measures have already been taken?
- What are your greatest challenges?

We look forward to talking to you about possible joint perspectives for the future.



Industry 4.0, in all its many facets, can only succeed if all those involved: end users, mechanical engineers, technology suppliers and the scientific world – all pull together.

Much more than just remote maintenance: Remote Services & Analytics offer added value for OEMs and end users.

Industry 4.0 is based on the digital networking of machines, products and components – and people as well, of course.

We provide a secure platform for remote maintenance in that we link the service technician to the machine with a connection that can be monitored. The machine operator, therefore, has the assurance that only authorized people can gain access to the machine and can do so only at the selected time.

Additionally, data can be collected from the machines and saved to a private 'cloud'. The data is then analyzed and converted into key figures that enable deeper insight into how the machines are functioning. We offer you a complete cloud-based quality management system. All cloud services are available in the form of a flexible subscription service, which makes the online transfer of machine data scalable. This has several advantages over an in-house system. IT investment, costly software licenses and maintenance are unnecessary. What is also decisive is the fact that complex, individual programming is rendered superfluous.

Undoubtedly, the most secure solution: The maximum security level “Financial Grade Security”

- Encrypted data from the network to the cloud
- NCP standard
- Transparent data exchange in the company network

Ready for the future

- OPC-UA/MQTT access to Lenze controllers
- Permanent data transfer to the cloud
- All data is available for immediate or future analysis

Plant management


- Monitoring of machine utilization and availability

Remote Maintenance

- Worldwide data access
- Remote diagnostics and servicing
- Reduces field service assignments by up to 80%

Predictive maintenance/Digital services



- Predictive detection of potential faults on the basis of the “cloud data”
- “Big data” as the basis for advisory services for production optimization by the OEM



Mobile racking: More storage space in a very small area.


- Soft starting and braking with adjustable ramps mean less strain and stress on material and goods being transported, while simultaneously reducing the amount and cost of maintenance work needed
- Flexible installation concepts due to decentralized and central drive technology
- Highly efficient drive technology with multiple overload capacity
- Reduced energy consumption due to savings during idling and partial-load operation, as well as the use of the “VFC eco” energy saving function
- High degree of reliability due to 70 years experience in the area of materials handling technology







Belt, roller and chain conveyors: Efficiency in motion.

- Simple and efficient decentralized drive solution for variable and fast conveying speeds of horizontal material handling systems
- High degree of reliability due to 70 years experience in the area of material handling technology
- Reduced energy consumption due to savings during idling and partial-load operation, as well as the use of the “VFC eco” energy saving function
- Soft starting and braking with adjustable ramps mean less strain and stress on material and goods being transported, while simultaneously reducing the amount and cost of maintenance work needed
- Minimal installation and wiring complexity due to decentralized drive concept
- Compact drive solution for constant speeds, even in the case of heavy load






Corner transfer conveyors: Successfully changing the direction.

- Compact drive solution for constant speeds, even in the case of heavy load
- Soft starting and braking with adjustable ramps mean less strain and stress on material and goods being transported, while simultaneously reducing the amount and cost of maintenance work needed.
- Minimal installation and wiring complexity due to decentralized drive concept
- High degree of reliability due to 70 years experience in the area of materials handling technology
- Reduced energy consumption due to savings during idling and partial-load operation, as well as the use of the “VFC eco” energy saving function





Control level



Field level

Actuator/sensor level – electromechanics

Lifting stations: For the strictest requirements.

- High degree of reliability where great heights have to be overcome thanks to low-wear brake management
- As the load is held in position, the brake is not applied so there is less stress on the material
- Fast and easy replacement during maintenance due to pluggable technology
- Reduced energy consumption due to power recovery in the case of very great heights





Control level


Field level

Actuator/sensor level – electromechanics

Carousel storage system: Optimum use made of storage space.

- High degree of warehouse availability due to efficient automation solutions with tried-and-tested technology
- High degree of reliability due to 70 years experience in the area of drive technology
- Highly efficient drive technology with multiple overload capacity and reduced energy consumption due to highly efficient gearboxes
- Reduced energy consumption due to savings during idling and partial-load operation, as well as the use of the “VFC eco” energy saving function






Storage and retrieval unit: Highly automated warehouse worker

- Complete solution package for advanced storage and retrieval units of the next generation
- Easy commissioning due to ready-made technology functions
- More available storage capacity due to reduction of buffer zones
- High degree of reliability due to decades-long experience with storage and retrieval units
- Reduced energy consumption with DC bus connection of traveling and lifting drives
- Regenerative modules for optimum energy balances





Efficient in all respects.

Energy-efficient with Lenze BlueGreen Solutions

On the basis of a holistic consideration of the tasks involved, we will show you how the energy efficiency of your drive applications can be increased with intelligent drive and automation technology. We will also assist you with adherence to important standards and laws.

Three approaches are pursued in order to increase the energy efficiency of drives:

1. Using electrical energy intelligently and using as little as possible


- Needs-based dimensioning
- Controlled operation (frequency inverter)
- Energy-efficient motion control

2. Converting energy with a high degree of efficiency

- Components with a high degree of efficiency (motors, gearboxes)

3. Using regenerative braking energy

- Energy exchange between several drives
- Temporary storage of braking energy
- Regeneration of braking energy and potential energy




Efficient drive sizing with Drive Solution Designer (DSD)



Intelligent drive design is the basis for a drive system that has the right components, exact dimensioning and is therefore as small as possible. Thanks to DSD, energy saving potential is apparent at a glance and is documented in the Energy Performance Certificate. A clear comparison of a different solution is made easy.

The reason is that DSD incorporates extensive and useful systems-design knowledge – with solidly based drive-applications know-how in areas such as drive physics, variants and energy efficiency. Drive design is based on calculations with individual process data and on speed profiles, and takes into account the complete drive structure for the requirements of the machine in question.


In our DSD training course, we will familiarize you with this engineering tool and show you how easy it is to use.



Energy exchange via DC bus connection



Comparison of DC supply



Comparison of drive axes

A powerful performance in any situation.


In order to meet the special requirements involved in warehouse logistics, you can place your trust in our drive design know-how accumulated over many years and also in our adapted and coherent product portfolio. This is the basis for a robust solution that has been adapted to the conditions of the respective plant location.

As a result, it is possible to react to power failures due to unstable power grids without any damage being done to the equipment.

Ready for anything:


- Well thought-out systems enable device replacement during ongoing operation
- Products for low-noise use
- Scalability of products considerably reduces the variety of devices needed
- Weight reduction due to the use of light-metal materials
- Suitable for special ambient conditions, e.g. deep-frozen goods temperatures





Reducing the number of different drive versions with ease

- Quadruple overload capacity
- Decentralized drive solutions
- Reduction of the variants of devices by up to 70%
- Reduced stock
- Parameterization by means of NFC



Prepared for special ambient conditions

- Optimum corrosion protection in the fresh-goods temperature range of 32°F to 59°F (0 to +10°C)
- Rust-free design
- OKS-L paints
- Special torque reserve and adaptations of the gearbox oil and seals in the deep-frozen goods range of 32°F to -22°F (0 to -30°C)



Fast and easy replacement during maintenance

- Aluminium gearbox instead of heavy grey cast iron gearbox
- Pluggable connection system
- Parameterization by means of NFC
- Connection dimensions standard in industry




Needs-based drive design with Drive Solution Designer (DSD)

- In-depth knowledge about drive applications such as drive physics, variants and energy efficiency
- Calculations with individually applicable process data and speed profiles
- Complete drive structure for all of the machine's requirements
- Energy Performance Certificate makes savings potential visible at a glance

Worldwide service for the requirements of warehouse logistics.

Productivity, reliability and new peak levels of performance every day – these are our decisive success factors for your system. We offer individually designed service concepts for permanently safe and reliable operation. Our service modules, combined with our expert

support, are based on the excellent application know-how of our experienced specialists. Wherever, whenever, and however you need our support, we are always there to help you.



Lenze inspection

What is the current status?

You know your machine exactly. Working with you closely, we create the basis for suitable measures. For example, we uncover weak points or risks and find value performance reserves. One thing is certain, with us, your machine is in the very best hands.

Lenze prevention

Prepared for the unexpected.

Our comprehensive preventive service is the ideal way to minimize potential risks to your machine. We support you in increasing machine availability, and minimizing reaction times and downtimes in the event of faults, saving you time and money.



Lenze optimization

Making good things even better.

We ensure that your systems work perfectly, and show you intelligent optimization possibilities including: reducing energy costs, shortening set-up times for production changeovers, and improving efficiency. We take care of it all.

Lenze emergency service


Perfectly equipped to handle any challenge.

You can depend on us in the event of an emergency. We make extensive preparations for potential problems. Should something unforeseen occur, we will make sure that your systems are back up and running quickly, and perform an in-depth error analysis. With us, your projects are in safe hands.

Lenze makes many things easy for you: In every phase of the engineering process.

We always work closely with you to find the very best solution and enthusiastically work to set your ideas in motion. Regardless of whether you want to improve existing equipment or develop a completely new machine or

application for overall warehouse logistics systems. We always strive to make things easy and seek perfection therein. This is anchored in our thinking, in our services and in every detail of our products.





www.Lenze.com

This document is the intellectual property of Lenze SE, Hamelin (Germany). All details and information included in this brochure are correct based on the information available at the time of publishing and serve only to provide preliminary information. Potential color deviations from the original product are due to the printing process. Lenze is the sole and exclusive owner of the copyright and the intellectual property rights. Any use of this document, in particular dissemination, reprinting or adapting, it is only permitted following express written approval by Lenze.

13550914

Lenze